














Precision ESD Safe Phillips Screwdrivers



SKU	Product	Size Phillips
27302	 Precision ESD Safe Phillips #000 x 40mm	#000
27305	 Precision ESD Safe Phillips #00 x 40mm	#00
27307	 Precision ESD Safe Phillips #00 x 75 mm	#00
27310	 Precision ESD Safe Phillips #0 x 50mm	#0
27312	 Precision ESD Safe Phillips #0 x 75mm	#0
27314	 Precision ESD Safe Phillips #0 x 100mm	#0
27316	 Precision ESD Safe Phillips #0 x 150mm	#0
27320	 Precision ESD Safe Phillips #1 x 60mm	#1
27322	 Precision ESD Safe Phillips #1 x 75mm	#1
27324	 Precision ESD Safe Phillips #1 x 100mm	#1
27326	 Precision ESD Safe Phillips #1 x 150mm	#1

Details

Wiha special chrome-vanadium-molybdenum tool steel
 Through hardened for best wear resistance
 Corrosion protective Hard Chrome Finish
 Exact Fit Precision Machined Tips
 Precision Handle is made of high Quality cadmium free Plastic
 ESD-Safe Dissipative Material
 Molded on handle for permanent bond to Blade
 The Tapered Shape allows rapid rotation
 Handles Proportioned to Blade Size for optimum torque
 Precision Turning and Control with the Rotating Cap

Additional Info

RoHS Compliant	Yes
ESD Safe	Yes
Head Type	 phillips
Handle Grip Types	ESD safe, Precision

