








TorqueVario Adjustable Inch Pounds Handles



SKU	Product	Range Inch lbs.	Imperial Increments	Torque Accuracy
28501	 Adjustable TorqueVario 15 - 80 In/Oz	15 - 80 in/oz	2.5 inch ounces	±10%
28502	 Adjustable TorqueVario 5 - 10 In/lbs	5 - 10	0.5 inch pounds	±6%
28404	 Adjustable TorqueVario 5 - 18 In/lbs	5 - 18	0.5 inch pounds	±6%
28408	 Adjustable TorqueVario 18- 62 In/lbs	18-62	2 inch pounds	±6%
28506	 Adjustable TorqueVario 10 - 50 In/lbs	10 - 50	2 inch pounds	±6%

Details

EN ISO 6789, BS EN 26789, ASME B107.14M
 Tools Marked with Serial No. & Include Calibration Certificate
 Ergonomic Multi-Component Handle, particularly light and compact
 Handle sizes proportioned to optimize torque range
 Audible and perceptible click when the pre-set torque has been attained
 ±6% Accuracy
 Quality & Accuracy Guaranteed to 5000 Cycles or 1 year
 Secure Torque Setting, comes with torque adjustment tool
 Loosening torque approx. +30% greater than tightening torque
 Automatically resets for next torque cycle
 Includes TorqueControl Adapter Blade For 4mm Bits

Additional Info

RoHS Compliant	Yes
TorqueControl Type	Adjustable TorqueVario
Handle Grip Types	SoftFinish®
Torque Display Scale	Inch - lbs

