



# Phillips SoftFinish® Screwdrivers



SKU	Product	Size Phillips	Blade Length Inch	OAL MM
31105	 SoftFinish® Phillips Driver #0 x 60mm	#0	2.4	164
31110	 SoftFinish® Phillips Driver #1 x 80mm	#1	3.1	191
31112	 SoftFinish® Phillips Driver #1 x 200mm	#1	8	311
31114	 SoftFinish® Phillips Driver #1 x 300mm	#1	12	411
31115	 SoftFinish® Phillips Driver #2 x 100mm	#2	3.9	218
31117	 SoftFinish® Phillips Driver #2 x 200mm	#2	8	318
31118	 SoftFinish® Phillips Driver #2 x 300mm	#2	12	418
31120	 SoftFinish® Phillips Driver #3 x 150mm	#3	5.9	274
31125	 SoftFinish® Phillips Driver #4 x 200mm	#4	8	323

## Details

### Wiha SoftFinish Handle

- > Dual material molded improves comfort and performance.
- > Through ergonomic design the handle allows 40% more torque and less hand fatigue than conventional handles.
- > Handle with roll-off protection feature.

### Wiha Screwdriver Tips

- > Wiha tips are precision machined to exact tolerances for a perfect fit every time.
- > Wiha utilizes an exclusive chrome-vanadium-molybdenum tool steel.
- > Through hardened to 60 on the Rockwell C scale.

### Wiha Hard Chromtop Plating

- > Provides additional unmatched durability for tips and blade integrity.

## Additional Info

RoHS Compliant	Yes
Head Type	 phillips
Handle Grip Types	SoftFinish®
Steel HRC	60