



Straight Internal Retaining Ring Pliers



SKU	Product	Ring Diameter Range Inch	Ring Diameter Range mm	Tip size inch	Tip size mm
32681	Internal Ring Pliers 5/16 - 1/2"	5/16-1/2	8-13mm	.035	0.9mm
32682	Internal Ring Pliers 1/2 - 1"	1/2-1	12-25mm	.050	1.3mm
32683	Internal Ring Pliers 3/4 - 2 3/8"	3/4-2 3/8	19-60mm	.070	1.5mm
32684	Internal Ring Pliers 1.5 - 4"	1 1/2-4	40-100mm	.090	2.3mm
32654	Internal Ring Pliers 3.5 - 5.5"	3.5-5.5	85-140mm	.126	3.2mm

Details

High quality C70 forged Tool Steel
Precision machined exact fit tips
Slim Plier Head for optimal Access
Soft Vinyl Grip Handles are Oil and Solvent Resistant
Professional quality made by Wiha

Additional Info

Grip Type	Vinyl
Pliers Type	Retaining Ring
RoHS Compliant	Yes
Ring Type	Internal

