













Security Torx® Insert Bit




SKU	Product	Security Torx Size	
70127	 Security Torx® Insert Bit T7s - 10 PACK	T7s	
70128	 Security Torx® Insert Bit T8s - 10 PACK	T8s	
70129	 Security Torx® Insert Bit T9s - 10 PACK	T9s	
70168	 Security Torx® Insert Bit T40s - 10 PACK	T40s	
70135	 Security Torx® Insert Bit T10s - 10 PACK	T10s	
70142	 Security Torx® Insert Bit T20s - 10 PACK	T20s	
70148	 Security Torx® Insert Bit T25s - 10 PACK	T25s	
70160	 Security Torx® Insert Bit T27s - 10 PACK	T27s	
70163	 Security Torx® Insert Bit T30s - 10 PACK	T30s	
70139	 Security Torx® Insert Bit T15s - 10 PACK	T15s	

Details

Wiha premium bits - exact fit precision machined
Universal fit for all standard bit holders & power tools
Wiha special chrome-vanadium-molybdenum tool steel
Torx is a 100% improvement in drive performance over other systems
Virtually eliminates screw head cam-out
Through hardened for best wear resistance
Security Bits can also be used as regular Torx Bits

Additional Info

RoHS Compliant	Yes
Head Type	 security torx
Pack Quantity	10 Bits
Material	Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened
Bit Drive Size	1/4" Hex
Coating	Standard
ISO Standard Size	C6.3
Machine Hardness	HRC 59-61
Bit Length	25mm~1"