

3.5mm Right Angle Mini Plug


pro-SIGNAL



Specifications

Connector Type	: RCA / Phono
No. of Contacts	: 2
Gender	: Plug
Connector Colour	: Black
Contact Termination	: Solder
Pin Size	: 3.5mm
Connector Mounting	: Cable
Insulation Resistance	: 100MΩ Min. @ 500V DC
Dielectric Strength	: 500V AC for a minute

Diagram



Dimensions : Millimetres

No.	Part Name	Material	Finish	Qty.
1.	Contact A	Brass	Ni	1
2.	Insulator A	Ebonite	-	
3.	Contact B	Steel	Ni	
4.	Insulator B	Ebonite	-	
5.	Terminal	Brass	Ni	
6.	Pin	Steel	Ni	
7.	Cap	P.P	-	
8.	Protector	PVC	-	

Part Number Table

Description	Part Number
3.5mm Right Angle Mini Plug	MP-011LN

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell Limited 2016.