Data Sheet



Coaxial Panel Connector 23_BNC-50-0-12/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 4 \ \text{GHz} \end{array}$

Mechanical Data

Number of matings 500
Weight 0.0105 kg

Environmental Data

Operating temperature -65 °C to 165 °C 2011/65/EU (RoHS) compliant

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |

Related Documents

 Outline drawing
 DOU-00011017

 Catalogue drawing
 DCA-00011018

 Mounting hole
 DOU-0009051

Ordering Information

Single package 23_BNC-50-0-12/133_NE