



RoHS Compliant



ITEM NO.	LENGTH	TOLERANCE	QBAG(mm)
USB3C-DVI-1M	1000mm	30mm	0.1*180*220
USB3C-DVI-2M	2000mm	30mm	0.1*180*220
USB3C-DVI-3M	3000mm	30mm	0.1*180*220
USB3C-DVI-5M	5000mm	50mm	0.1*200*250



1PCS/QBAG-X(0.10*XXX*XXXmm)+Sticker

Electrical Test:

- 1.Real Test Passed 3840 * 2160P 30Hz.
- 2.Real Test Not Twinkling,Double Vision and Decolor.

NUMBER	PRODUCT SPECIFICATIONS	Quantity	Unit
5	BLACK 45P PVC		G
4	SCREW:#4-40UNC(Black Moldin,Nickel Plated)	2	PCS
3	DVI 24+1P MALE(Black Insulator,Gold Plated)+PCB'A	1	PCS
2	USB Type-C MALE(White Insulato,Gold Plated)	1	PCS
1	NON-UL,(32#*1P+D+AL/MY)*5+32#*4C+24#*2C+AL+B OD=4.8mm,BLACK TPE JACKET.	1	PCS

D		
C		
B		
VER.A	REVISE	DATE
Item	USB3C-DVI-XM	
Draw	Hobe	Date: 2017.12.28
Approval		
Maker	F16	
Sample NO.	Drawings of 1 (1) Proportion: 1:1 Unit(mm)	