



(0.50 mm) .0197"

MEC5-DV, MEC5-RA SERIES

VERTICAL/RIGHT-ANGLE CARD SOCKET

Mates with:

(1.60 mm) .062" thick card with standard board tolerance

SPECIFICATIONS


For complete specifications and recommended PCB layouts see www.samtec.com?MEC5-DV

Insulator Material:
Black LCP
Contact Material:
Phosphor Bronze
Plating:
Au or Sn over
50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +125 °C
Current Rating:
1.5 A per pin
(2 pins powered)
Voltage Rating:
125 VAC/175 VDC
RoHS Compliant:

PROCESSING

Lead-Free Solderable: Yes

Note: Some sizes, styles and options are non-standard, non-returnable.



Mates with:

(1.60 mm) .062" thick card with standard board tolerance

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MEC5-RA

Insulator Material:
Black LCP
Contact Material:
Phosphor Bronze
Plating:
Au or Sn over
50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +125 °C
Current Rating:
1.5 A per pin
(2 pins powered)
Voltage Rating:
125 VAC/175 VDC

PROCESSING

Lead-Free Solderable:

RoHS Compliant:

Note: Some sizes, styles and options are non-standard, non-returnable.

