

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1062250010](#)
Status: **Active**
Overview: [Optical Connectivity Solutions](#)
Description: MPO Female-to-MPO Female Trunk Cable Assembly, 9/125µm, 4.80mm, Singlemode, 12 Fiber, Plenum, OS2, 25.0m Length, Yellow

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Fiber Optic Assemblies
Series	106225
Boot Type	Straight
Connector to Connector	MPO-to-MPO
Mode	Singlemode
Overview	Optical Connectivity Solutions
Product Name	MPO
UPC	191128250221


Physical

Cable Length	25.0m
Cable Size	4.80mm
Fiber (Core/Cladding)	9/125µm
Net Weight	551.853/g
Single Ended	No
Wire/Cable Type	12 Fiber OS2 Plenum

Material Info

Reference - Drawing Numbers

Sales Drawing	1062250000-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[106225](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION