

ROLINE HQ VGA Cable + Ferrite, HD15, M/M, 10.0 m

Product No.	11.04.5260
Manufacturer	ROLINE
Manufacturer No.	11.04.5260
EAN (single piece)	7611990120802



- High quality cable for connection of a monitor to a graphics card or VGA splitter or amplifier
- As monitor connection cable with two additional ferrite cores
- 3 coax lines for the RGB signals and 7 AWG28 wires
- Connector casings moulded
- Double screened cable (braided and foil shield)
- Hand locking screws

Technical specifications

Manufacturer	ROLINE
Product group	Cable
Product type	VGA Cables
Colour	black
Length	10 m

side 1 connector	D-Sub HD 15 Male
side 2 connector	D-Sub HD 15 Male
Side 1 Connector Type	HD D-Sub 15-pin (HD-15), VGA
Side 1 Connector Gender	Male
Side 2 Connector Type	HD D-Sub 15-pin (HD-15), VGA
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Double screened
Hand locking screws	Yes
Cable composition	3 Coax RGB 7xAWG28
Technical particularity	with ferrite