

Datenblatt - Fiche technique - Data sheet **12.03.3200**



ROLINE Typ C - VGA Adapter, ST/BU


ROLINE Adaptateur Type C - VGA, M/F

ROLINE Type C - VGA Adapter, M/F



Item no.: 12.03.3200 ROLINE USB 3.1 Cable Adapter, C – VGA, M/F Aluminum, silver





Features:

- Support VGA Video output 1080P@60Hz resolution
- Aluminum Housing in silver color
- No driver needed
- USB 3.1 Type-C interface supports plug and play, hot swap
- Easy to carry and use
- With 10cm Cable in white color
- Connector: USB 3.1 Type-C Male*1 (input) + HD VGA Female*1 (output)
- Operating Temperature: 0°C~45°C
- Storage Temperature: -20°C ~ 70°C
- Operating Humidity: 10% ~ 85 % RH (no condensation)
- System requirements: Windows, MAC OS X, Google Chrome

USB 3.1 Type-C[™] to VGA Socket Converter

User Manual



Contents

1.0 INTRODUCTION	1
2.0 FEATURES	1
3.0 SPECIFICATIONS	1
4.0 PACKAGE CONTENTS	2
5.0 OPERATION	2
6.0 CONNECTION DIAGRAM	2

USB 3.1 Type-C™ to VGA Socket converter

DEAR CUSTOMER

Thank you for purchasing this product. For optimum performance and safety, please read these instructions carefully before connecting, operating or using this product. Please keep this manual for future reference.

1.0 INTRODUCTION

This is a USB 3.1 Type C^{TM} to HD15 VGA Socket, designed for connecting VGA Monitor to host computer, the host computer can easily connect to the Monitor. Connecting the projector with a VGA cable which is contacted with the VGA socket of this converter. It can work on Mac book or Google new Chromebook Pixel or Asus Zen AiO and other USB 3.1 Type C^{TM} supported devices.

2.0 FEATURES

- Support USB-Type C[™] Video output 1080P@60hz resolution
- NO driver needed
- ABS Housing Provide white, black two colors
- Aluminium Housing Provide gold, silver, grey space, three colors
- Slim Type ABS Housing Provide white, black two colors
- With 10cm Cable
- USB 3.1 Type C[™] interfaces support plug and play, hot swap
- Easy to carry and use

3.0 SPECIFICATIONS

Item No.:	
ABS Housing	716091 716091S
ABS Slim Type	716103 716103S
Aluminium Housing	716091V 716091D 716091X
Size(L*W*H)	
ABS Housing	200*45*15.2mm
ABS Slim Type housing	200*25*11.5mm
Aluminium Housing	200*38*13mm
Input/Output Connector	
Input port	USB 3.1 Type-C™ Male*1
Output port	HD15 VGA Socket
Warranty	
Limited Warranty	1 Year
Environmental	
Operating Temperature	0℃~45℃

Operating Humidity	10% ~ 85 % RH (no
	condensation)
Storage Temperature	-20℃~ 70℃
Storage Humidity	5% ~ 90 % RH (no condensation)
System requirements	Windows, MAC OSX, Google
	Chrome
Regulatory Approvals	
	FCC CE Certification
	RoHS 2.0 & REACH Compliant
Accessories Adapter	
User Manual	English Version

4.0 PACKAGE CONTENTS

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the shipping carton:

- Main unit x1
- User Manual x1

5.0 OPERATION

- 1) Connect the VGA Socket to Monitor
- 2) Connect the USB 3.1 Type $C^{\scriptscriptstyle\mathsf{TM}}$ male port of this product to computer

6.0 CONNECTION DIAGRAM

