

LED Floodlights



VT-10-W

HIGHLIGHTS :

WATTS



10

EQ. WATTS



LUMINOUS



800

BEAM ANGLE



100

PRODUCT FEATURES

Item No	: VT-10-W
SKU Code	: 427
Watts	: 10
Voltage	: AC:220-240V,50Hz
Lumen(lm)	: 800
Color Temperature	: 3000K
Beam Angle	: 100
PF	: >0.9
LED Chip Type	: SMD-Samsung Chip
CRI	: >80
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP65
Body type	: Die casting Aluminium
Dimmable	: -
Life Time	: 30,000 Hours
Operation Temperature	: -25 to +50°C
EAN code	: 3800157630832
Unit size	: 115x108x26mm
Packing details	: 20.00