

## LED Spotlights



VT-203

### HIGHLIGHTS :

WATTS



2.5

EQ. WATTS



20

LUMINOUS



200

BEAM ANGLE



300

### PRODUCT FEATURES

|                            |   |                  |
|----------------------------|---|------------------|
| Item No                    | : | VT-203           |
| SKU Code                   | : | 245              |
| Watts                      | : | 2.5              |
| EQ. Watts                  | : | 20               |
| Base / holder              | : | G9               |
| Voltage                    | : | AC:220-240V,50Hz |
| Lumen(lm)                  | : | 200              |
| Color Temperature          | : | 6400K            |
| Beam Angle                 | : | 300              |
| PF                         | : | >0.4             |
| LED Chip Type              | : | SMD-Samsung Chip |
| CRI                        | : | >80              |
| Energy rating label        | : | A+               |
| IP Rating Protection Class | : | IP20             |
| Body type                  | : | Plastic          |
| Dimmable                   | : | No               |
| Life Time                  | : | 30,000 Hours     |
| EAN code                   | : | 3800157632652    |
| Unit size                  | : | 16.5x 46.5mm     |
| Packing details            | : | 500.00           |