

LED Bulb Series



VT-230

HIGHLIGHTS :

WATTS



11

EQ. WATTS



95

LUMINOUS



825

BEAM ANGLE



40

PRODUCT FEATURES

Item No	: VT-230
SKU Code	: 155
Watts	: 11
EQ. Watts	: 95
Base / holder	: E27
Voltage	: AC:220-240V,50Hz
Lumen(lm)	: 825
Color Temperature	: 6400K
Beam Angle	: 40
Commercial type	: PAR30
PF	: >0.5
LED Chip Type	: SMD-Samsung Chip
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP20
Body type	: Thermoplastic
Dimmable	: No
Life Time	: 30,000 Hours
EAN code	: 3800157627689
Unit size	: ø95x117mm
Packing details	: 30.00