

LED Bulb Series



VT-236

HIGHLIGHTS :

WATTS



5.5

EQ. WATTS



40

LUMINOUS



470

BEAM ANGLE



180

PRODUCT FEATURES

Item No	: VT-236
SKU Code	: 169
Watts	: 5.5
EQ. Watts	: 40
Base / holder	: E14
Voltage	: AC:220-240V,50Hz
Lumen(lm)	: 470
Color Temperature	: 4000K
Beam Angle	: 180
Commercial type	: P45
PF	: >0.5
LED Chip Type	: SMD-Samsung Chip
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP20
Body type	: Thermoplastic
Dimmable	: No
Life Time	: 30,000 Hours
EAN code	: 3800157627825
Unit size	: ø45x81mm
Packing details	: 200.00