

LED Filament Series



VT-287

HIGHLIGHTS :

WATTS



6

EQ. WATTS



60

LUMINOUS



806

BEAM ANGLE



300

PRODUCT FEATURES

Item No	: VT-287
SKU Code	: 292
Watts	: 6
EQ. Watts	: 60
Base / holder	: E27
Voltage	: AC:220-240V,50Hz
Lumen(lm)	: 806
Color Temperature	: 2700K
Beam Angle	: 300
Commercial type	: G125
PF	: >0.5
LED Chip Type	: Filament-Samsung Chip
CRI	: >80
Energy rating label	: A++
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20
Body type	: Glass
Dimmable	: No
Life Time	: 20,000 Hours
Operation Temperature	: -25 to +50°C
EAN code	: 3800157634700
Unit size	: 125x177mm
Packing details	: 20.00