

PT100 probe, insertion, 1 m



The SE015 is a platinum resistance thermometer probe for use in insertion applications.

SE015 PT100 probe specifications	
Temperature range	–75 to +250 °C
Accuracy	±0.15 °C @ 0 °C Class A
Dimensions	
Length	120 mm
Diameter	3.3 mm
Cable	1 m
Material	Stainless steel probe, PVC cable
Handle	Yes
Connector	4-pin mini-DIN