



Thermocouple type K, exposed tip, PTFE insulated, 3 m



The SE028 is an exposed junction thermocouple with PTFE insulated, 0.2 mm twisted pair conductor.

SE028 Thermocouple characteristics	
Tip diameter	1.5 mm
Tip temperature	-75 to +250 °C
Cable length	3 m (about 10 ft)
Plug type	Molded flat pin mini-plug