


## Underground UF Splice Kit

Accommodates waterproof splicing of #14 - #8 AWG UF copper wire.

- Connector set screws engage each wire securely for a solid splice.
- Minimum conductor size 14/2 with ground.
- Maximum conductor size 8/3 with ground.
- Rated at 600 V max.



Part #	Pkg Qty	Description
HST-1300	1 kit	Underground UF Splice Kit




**Kit Contains:**

Qty	Description
4	Screw Splice Connectors
1	8" Heavy-Wall Polyolefin Heat-Shrink Tubing with Watertight Adhesive Liner

## Underground Butt Splice Kit (#8 - #2 AWG)

Used for waterproof installation or repair of #8 - #2 AWG copper cable.

- 3/4" ID heat shrink tube
- 1/2" Ø x 1 1/2" brass butt splice
- Eliminates messy epoxies, tapes or mastics.
- Rated at 600 V max.



Part #	Pkg Qty	Description
HSB-28	1 kit	Butt Splice Kit



**Kit Contains:**

Qty	Description
1	Screw Splice Connectors
1	4" Heavy-Wall Polyolefin Heat-Shrink Tubing with Watertight Adhesive Liner

## Underground Butt Splice Kit (#14 - #8 AWG)

Used for waterproof repair of well pipe cables and splices of stranded cable #14 - #8 AWG.

- .4" ID heat shrink tube
- 1/4" Ø x 1 1/4" brass butt splice
- Rated at 600 V max.



Part #	Pkg Qty	Description
HST-WP	1 kit	Butt Splice Connector Kit



**Kit Contains:**

Qty	Description
1	Screw Splice Connectors
1	4" Heavy-Wall Polyolefin Heat-Shrink Tubing with Watertight Adhesive Liner

