



Sample photo

Order symbol: AR1084CHSST
Product nbr: 8561107
Description: PC Enclosure
Remarks: Hinged transparent cover
w/S.S. Quick release latch

EAN: 6418074067395
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
	Length	Width	Height		
mm:	254	203	102	ALBP108	Aluminum Back Panel
inch:	10.0	8.0	4.0	ADFP108	Dead Front Panel w/ screws
				ASP108	Aluminum Swing Panel
				ASPK108	Swing Panel Kit incl. Panel
				ASPHK10	Swing Panel Kit w/o Panel
				AMFL8	8" Mounting Flange Set
Materials:			Rating:		
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/IP67		
Base colour:	RAL 7035 -light grey		Electrical insulation: Totally insulated		
Cover screws material:	Stainless steel		Halogen free (DIN/VDE 0472, Part 815): 0		
Cover colour:	Clear transparent		UV resistance: UL 508		
Gasket material:	Polyurethane		Flammability Rating: UL 508		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		
Temperatures:					
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP108	Painted Steel Back Panel				

