

Order symbol: AR1084CHSS
Product nbr: 8561101
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
Quick release latch

EAN: 6418074067371
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
Length	Width	Height	ALBP108	Aluminum Back Panel	
mm:	254	203	ADFP108	Dead Front Panel w/ screws	
inch:	10.0	8.0	ASP108	Aluminum Swing Panel	
Materials:			ASPK108	Swing Panel Kit incl. Panel	
Material:	Polycarbonate		ASPHK10	Swing Panel Kit w/o Panel	
Base colour:	RAL 7035 -light grey		AMFL8	8" Mounting Flange Set	
Cover screws material:	Stainless steel		Rating:		
Cover colour:	RAL 7035 -light grey		Ingress Protection (EN 60529): IP66/IP67		
Gasket material:	Polyurethane		Electrical insulation: Totally insulated		
Temperatures:			Halogen free (DIN/VDE 0472, Part 815): 0		
Temperature °C (short term):	-40 ... 140 °C		UV resistance: UL 508		
Temperature °C (continuous):	-40 ... 80 °C		Flammability Rating: UL 508		
Temperature °F (short term):	-40 ... 284 °F		Glow Wire Test (IEC 695-2-1) °C: 960		
Temperature °F (continuous):	-40 ... 175 °F		NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		
Accessories:					
ABP108	Painted Steel Back Panel				

