



Order symbol: AR864CHFSC
Product nbr: 8561623
Description: PC Enclosure
Remarks: Hinged opaque flat screw cover

EAN: 6418074097965
El. number:
Finland:

Including: Hinged screw flat cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

Dimensions:			Accessories:	
Length	Width	Height	ALBP86	Aluminum Back Panel
mm:	203	152	ADFP86	Dead Front Panel w/ screws
inch:	8.0	6.0	ASP86	Aluminum Swing Panel
Materials:			ASPK86	Swing Panel Kit incl. Panel
Material:	Polycarbonate		ASPHK8	Swing Panel Kit w/o Panel
Base colour:	RAL 7035 -light grey		AMFL6	6" Mounting Flange Set
Cover screws material:	Stainless steel			
Cover colour:	RAL 7035 -light grey		Rating:	
Gasket material:	Polyurethane		Ingress Protection (EN 60529): IP66/IP67	
Temperatures:			Impact Resistance (EN 62262): IK07/IK08	
Temperature °C (short term):	-40 ... 140 °C		Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 284 °F		UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F		Flammability Rating: UL 508	
Accessories:			Glow Wire Test (IEC 695-2-1) °C: 960	
ABP86	Painted Steel Back Panel		NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
			Certificates:	
			Gost R	

