



Sample photo

Order symbol: AR16148CHTSS
Product nbr: 8561066
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
Lockable twist latch

EAN: 6418074067203
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Length	Width	Height	Accessories:	
mm:			406	356	203	ALBP1614	Aluminum Back Panel
inch:			16.0	14.0	8.0	ADFP1614	Dead Front Panel w/ screws
						ASP1614	Aluminum Swing Panel
Materials:						ASPK1614	Swing Panel Kit incl. Panel
Material:			Polycarbonate			ASPHK16	Swing Panel Kit w/o Panel
Base colour:			RAL 7035 -light grey			AMFL14	14" Mounting Flange Set
Cover screws material:			Stainless steel				
Cover colour:			RAL 7035 -light grey				
Gasket material:			Polyurethane				
Temperatures:						Rating:	
Temperature °C (short term):			-40 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):			-40 ... 80 °C			Electrical insulation: Totally insulated	
Temperature °F (short term):			-40 ... 284 °F			Halogen free (DIN/VDE 0472, Part 815): 0	
Temperature °F (continuous):			-40 ... 175 °F			UV resistance: UL 508	
						Flammability Rating: UL 508	
						Glow Wire Test (IEC 695-2-1) °C: 960	
						NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	
Accessories:							
ABP1614			Painted Steel Back Panel				

