

**Order symbol:** ARK14127CHSSLT  
**Product nbr:** 8561597  
**Description:** PC Enclosure  
**Remarks:** Hinged transparent cover w/S.S. Lockable latch. Base includes 1/2 and 3/4 inch knock-outs

**EAN:** 6418074097736  
**El. number:**  
**Finland:**

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:	
mm:	356	305	178	ALBP1412 Aluminum Back Panel
inch:	14.0	12.0	7.0	ADFP1412 Dead Front Panel w/ screws
				ASP1412 Aluminum Swing Panel
Materials:			ASPK1412 Swing Panel Kit incl. Panel	
Material:	Polycarbonate		ASPHK14 Swing Panel Kit w/o Panel	
Base colour:	RAL 7035 -light grey		AMFL12 12" Mounting Flange Set	
Cover screws material:	Stainless steel			
Cover colour:	Clear transparent			
Gasket material:	Polyurethane			
Temperatures:			Rating:	
Temperature °C (short term):	-40 ... 140 °C		Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):	-40 ... 80 °C		Impact Resistance (EN 62262): IK07/IK08	
Temperature °F (short term):	-40 ... 284 °F		Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F		Halogen free (DIN/VDE 0472, Part 815): 1	
			UV resistance: UL 508	
			Flammability Rating: UL 508	
			Glow Wire Test (IEC 695-2-1) °C: 960	
			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	
Accessories:				
ABP1412	Painted Steel Back Panel			

