



Sample photo

Order symbol: AR884CHSST
Product nbr: 8561095
Description: PC Enclosure
Remarks: Hinged transparent cover
w/S.S. Quick release latch

EAN: 6418074067340
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Length	Width	Height	Accessories:	
mm:			203	203	102	ABP88	Painted Steel Back Panel
inch:			8.0	8.0	4.0	ALBP88	Aluminum Back Panel
						ADFP88	Dead Front Panel w/ screws
Materials:						ASP88	Aluminum Swing Panel
Material:			Polycarbonate			ASPK88	Swing Panel Kit incl. Panel
Base colour:			RAL 7035 -light grey			ASPHK8	Swing Panel Kit w/o Panel
Cover screws material:			Stainless steel			AMFL8	8" Mounting Flange Set
Cover colour:			Clear transparent				
Gasket material:			Polyurethane				
Temperatures:						Rating:	
Temperature °C (short term):			-40 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):			-40 ... 80 °C			Electrical insulation: Totally insulated	
Temperature °F (short term):			-40 ... 284 °F			Halogen free (DIN/VDE 0472, Part 815): 0	
Temperature °F (continuous):			-40 ... 175 °F			UV resistance: UL 508	
						Flammability Rating: UL 508	
						Glow Wire Test (IEC 695-2-1) °C: 960	
						NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	
Accessories:							
APBP88			PVC Back Panel				

