



Sample photo

Order symbol: AR14127CHTSS
Product nbr: 8561050
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
Lockable twist latch

EAN: 6418074067067
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
	Length	Width	Height		
mm:	356	305	178	ALBP1412	Aluminum Back Panel
inch:	14.0	12.0	7.0	ADFP1412	Dead Front Panel w/ screws
				ASP1412	Aluminum Swing Panel
				ASPK1412	Swing Panel Kit incl. Panel
				ASPHK14	Swing Panel Kit w/o Panel
				AMFL12	12" Mounting Flange Set
Materials:			Rating:		
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Stainless steel				
Cover colour:	RAL 7035 -light grey				
Gasket material:	Polyurethane				
Temperatures:			Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (short term):	-40 ... 140 °C		Impact Resistance (EN 62262): IK07/IK08		
Temperature °C (continuous):	-40 ... 80 °C		Electrical insulation: Totally insulated		
Temperature °F (short term):	-40 ... 284 °F		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (continuous):	-40 ... 175 °F		UV resistance: UL 508		
Accessories:			Flammability Rating: UL 508		
ABP1412	Painted Steel Back Panel		Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		

