

**Order symbol:** ARK14127CHSCT  
**Product nbr:** 8561589  
**Description:** PC Enclosure  
**Remarks:** Hinged transparent screw cover, base includes 1/2 and 3/4 inch knock-outs.

**EAN:** 6418074097651  
**El. number:**  
**Finland:**

Including: Hinged screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
mm:	Length	Width	Height		
mm:	356	305	178	ALBP1412	Aluminum Back Panel
inch:	14.0	12.0	7.0	ADFP1412	Dead Front Panel w/ screws
				ASP1412	Aluminum Swing Panel
				ASPK1412	Swing Panel Kit incl. Panel
				ASPHK14	Swing Panel Kit w/o Panel
				AMFL12	12" Mounting Flange Set
Materials:					
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Stainless steel				
Cover colour:	Clear transparent				
Gasket material:	Polyurethane				
Temperatures:					
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP1412				Painted Steel Back Panel	
Rating:					
				Ingress Protection (EN 60529): IP66/IP67	
				Impact Resistance (EN 62262): IK07/IK08	
				Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 508	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	

