

Order symbol:	ARK1086SCT
Product nbr:	8561505
Description:	PC Enclosure
Remarks:	Transparent screw cover. Base includes 1/2 and 3/4 inch knock-outs.

EAN: 6418074096814
El. number:
Finland:

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:
mm:	254	203	152	ALBP108 Aluminum Back Panel
inch:	10.0	8.0	6.0	ADFP108 Dead Front Panel w/ screws
Materials:				ASP108 Aluminum Swing Panel
Material:	Polycarbonate			ASPK108 Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPHK10 Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel			AMFL8 8" Mounting Flange Set
Cover colour:	Clear transparent			
Gasket material:	Polyurethane			
Temperatures:				Rating:
Temperature °C (short term):	-40 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK07/IK08
Temperature °F (short term):	-40 ... 284 °F			Electrical insulation: Totally insulated
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1
Accessories:				UV resistance: UL 508
ABP108	Painted Steel Back Panel			Flammability Rating: UL 508
				Glow Wire Test (IEC 695-2-1) °C: 960
				NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13

