



Static Eliminator QUICK440A



Features:

- Compact size, light, portable design, adjustable angle.
- Quickly neutralizes static charges.
- Large area of ionizing air.
- Speed of fan adjustable, can generate large-area ion stream.
- Stable and adjustable ion balance.
- Long lifetime magnetic leakage transformer, can protect the unit from short circuit.
- Built-in emitter cleaner, easy cleaning.

Specifications:

Power Consumption	30 W
Output Voltage	AC 5.6KV
Ion Balance	$\leq \pm 10V$
Air Volume	$\leq 2.4m^3/min$
Effective Range	400×1500mm
Ozone Production	$\leq 0.03ppm$ (150mm from center of air outlet)
Noise	45dB
Ambient Temperature	0°C-40°C
Dimensions	140(L)×84(W)×220(H)mm
Weight	About 2.6 Kg