



Classic filament LED Lamps

CLA LEDCandle D 5-40W BA35 E14 827 CL

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	5-40W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Luminous Flux (Rated) (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (Rated) (Nom)	94.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W


Lamp Current (Nom)	28 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh

Classic filament LED Lamps

Product Data	
Full product code	871869670996200
Order product name	CLA LEDCandle D 5-40W BA35 E14 827 CL
EAN/UPC - Product	8718696709962
Order code	929001332802
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001332802
Net Weight (Piece)	0.020 kg




Dimensional drawing



Candle BA35 4.5-40W 470lm 2700K D Clear

Product	D	C
CLA LEDCandle D 5-40W BA35 E14 827 CL	35 mm	129 mm


Photometric data




LEDbulb 40W E14 827 CL B35

Classic filament LED Lamps

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

