



120W

VT-9-120 120W HIGHBAY(MEANWELL DRIVER)WITH SAMSUNG CHIP
COLORCODE:6400K 5 YRS WARRANTY

Lumens
21600

Beam Angle
120

Dimensions
Ø260x145mm

White
SKU:569

5 YEARS
WARRANTY



Technical Information

Instant Start: 1-10V

Watts: 120

Lumens: 21600

Beam Angle: 120

Unit Color: Black

Body Type: Aluminum

Long life: 30,000 Hours

LED Chip Type: SMD

IP Rating: IP65

Dimmable: No

Warranty (Years): 5

PF: >0.9

CRI: >80

Input Power: AC:100-277V,50/60Hz

Features

- ✓ Powerful LED light source with a unique design
- ✓ High Power LED Samsung Chip
- ✓ Reflector options of beam angle 90°D / 120°D
- ✓ High Lumen highbay with Meanwell Driver - 1-10V Dimmable
- ✓ Longevity and efficient lumen Maintenance
- ✓ High Thermal Conductivity, Low Luminous Decay, Pure Colours & No Heavy Shade
- ✓ Complies with LM-80
- ✓ Applications - Industrial Usage, Warehouse & Super Markets, Workshop's, Factories, Warehouse's and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Listing Details

EAN Code

[3800157633338](#)

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES