

LED Bulb Series



VT-295

HIGHLIGHTS :

WATTS



12

EQ. WATTS



100

LUMINOUS



1521

BEAM ANGLE



200

PRODUCT FEATURES

Item No	:	VT-295
SKU Code	:	250
Watts	:	12
EQ. Watts	:	100
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	1521
Color Temperature	:	4000K
Beam Angle	:	200
Commercial type	:	A65
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A++
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157633604
Unit size	:	ø66.5x134mm
Packing details	:	100.00