

Telephone Modular Cable - 3m

RJ11 Plug - RJ11 Plug (6P4C)

pro-SIGNAL





Specifications:

Cable Length	: 3m/9.8ft
Connector Type A	: RJ11 Plug
Connector Type B	: RJ11 Plug
Cable Wiring	: 30AWG (7/0. 10CU)×4C
Outer Diameter	: 4.8*2.4mm ±0.1mm
Jacket Material	: PVC
Cable Colour	: Black
Connector Insulation	: Clear Polyester
Connector Contact	: Brass, Gold Plated
Conductive Resistance	: 3Ω
Insulation Resistance	: 5MΩ Min.



RoHS
Compliant

Diagram:



SIDE: A		SIDE: B
6P4C M		6P4C M
2	BLACK	2
3	RED	3
4	GREEN	4
5	YELLOW	5

Pin Out



Packing

Part Number Table

Description	Part Number
Telephone Modular Cable, RJ11 Plug - RJ11 Plug, 6P4C, Black, 3m	PS11457

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell Limited 2016.