

Product availability : Stock - Normally stocked in distribution facility



### Main

Disconnecter device type	Non-fusible disconnect switch
Enclosure type	Rainproof enclosure indoor/outdoor Ice/Sleet proof enclosure indoor/outdoor Dustproof enclosure indoor/outdoor
Series name	Heavy duty

### Complementary

Line Rated Current	30 A
AWG gauge	AWG 12...AWG 6 aluminium cable AWG 14...AWG 6 copper cable
Device mounting	Surface
Electrical connection	Lugs
Enclosure material	Galvannealed steel
Number of poles	3
Permissible voltage	<= 600 V
Short-circuit protection	<= 200 A
Switch function	TPST
Wiring configuration	Without neutral

### Environment

Contacts type and composition	1 NO/1 NC
NEMA degree of protection	NEMA 3R/12
Product certifications	UL listed

### Ordering and shipping details

Category	00113 - H&HU SW,2&3P,N12,30-200A
Discount Schedule	DE1

GTIN	00785901156536
Nbr. of units in pkg.	1
Package weight(Lbs)	10.279999999999999
Returnability	Y
Country of origin	US

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------