

Product data sheet

Characteristics

H362RB

SWITCH FUSIBLE HD 600V 60A 3P NEMA3R

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Single Throw Safety Switch
Line Rated Current	60 A
Product certifications	UL listed
NEMA degree of protection	NEMA 3R galvanized steel
Device composition	None
Disconnecter device type	Fusible disconnect
Short-circuit current	10 kA H or K 200 kA R, J or L
Device mounting	Surface
Number of poles	3
Electrical connection	Lugs
Series name	Heavy duty
System Voltage	600 V AC/DC
AWG gauge	AWG 14...AWG 3 (copper or aluminium)

Ordering and shipping details

Category	00009 - H&HU SW,2&3P,N3R,30-200A
Discount Schedule	DE1
GTIN	00785901482185
Nbr. of units in pkg.	1
Package weight(Lbs)	15.43
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity

 Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
