

Product data sheet

Characteristics

2510FG1

FHP Manual Starter - NEMA 1 - 1P - Toggle
 Operated - No Indicator - 277VAC

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Single Unit Manual Starter
Range of product	F
Thermal overload type	Melting alloy

Complementary

Line Rated Current	16 A
Cable entry	0.5" and 0.75" knock-outs (top and bottom)
Motor power hp	1 hp at 115 V AC 1 hp at 230 V AC 1 hp at 277 V AC
System Voltage	277 V AC
Poles description	1P
Control type	Toggle switch
Phase	1 phase
Local signalling	No indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 12 (copper)
Height	4.25 in
Width	2.44 in
Depth	2.75 in

Environment

Product certifications	CE CSA LR25490 class 3211 05 UL listed file E42243 CCN NLRV
------------------------	---

NEMA degree of protection

NEMA 1 plastic standard size

Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
GTIN	00785901553939
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7700000000000002
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
