LED Bulb G9, Clear Capsule

pro-**ELEC**

RoHS Compliant



Specifications

Lamp Style Lamp Base Type LED Colour Dimmable Luminous Flux Power Rating Voltage Rating Life Span On/Off Temperature CRI Quick Light **Beam Angle** Equivalent Power Efficiency Rating Power/1000h Dimensions (L × D) : Clear Capsule : G9 : Warm White : No : 255lm : 3W : 220-240V : 25000h : 15000x : 3000K : >80 : <1s : 270° (Deg.) : 22W : A+ : 3kWh/1000h : 56mm×15mm

Part Number Table

Description		Part Number
) Lamp, Clear Capsule, G9, Warm White, 3W, 15mm	PEL00051

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility of rits accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.farnell.com www.cpc.co.uk

