Product data sheet Characteristics

8536SCO3V02H30S

Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR, Open +Options



Product availability: Stock - Normally stocked in distribution facility

Price*: 648.00 USD



Main	
Product or component- type	Starter
Range of product	S
Control circuit	Separate control circuit

Complementary

- Complementary		
[Uc] control circuit voltage	110 V AC 50 Hz	
	120 V AC 60 Hz	
Motor starter type	Non reversing	
Line Rated Current	27 A	
Poles description	3P	
Phase	3 phases	
Rated power in HP	7.5 HP 200 V AC	
	7.5 HP 230 V AC	
	10 HP 460 V AC	
	10 HP 575 V AC	
System Voltage	600 V AC	
Control type	No control units	
Thermal overload type	Solid state Motor Logic class 10/20	
Electrical connection	Screw clamp terminals	
NEMA size	1	
Height	6.77 in (172 mm)	
Depth	4.21 in (107 mm)	
Width	3.5 in (89 mm)	

Environment

NEMA degree of protection	Not rated (open device)
Product certifications	NEMA
	UL listed CSA

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901807056
Nbr. of units in pkg.	1
Package weight(Lbs)	3.99000000000002
Returnability	Υ
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity
	Electric declaration of conformity

Contractual warranty

Warranty period	4	O mantha
Warranty period	II.	8 months
Trainanty ponoa		o monuto

Product Life Status :	Commercialised	
-----------------------	----------------	--