

**Blanking plugs
VP M20-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP M20-MS65
Order No.	1777740000
Version	Blanking plugs, Blanking plug, M 20, 6 mm, Brass, nickel-plated
GTIN (EAN)	4032248158010
Qty.	100 pc(s).

**Blanking plugs
VP M20-MS65**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	9.5 mm	Length (inches)	0.374 inch
Height	9.5 mm	Height (inches)	0.374 inch
Net weight	7.3 g	Diameter	22 mm

General information

Cable gland	metric	External thread	M 20
Head diameter	22 mm	Length of thread	6 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Protection degree	IP68
Sealing	NBR		

Classifications

ETIM 3.0	EC000032	ETIM 4.0	EC000032
ETIM 5.0	EC000032	ETIM 6.0	EC000451
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-10
eClass 6.2	27-14-91-10	eClass 7.1	27-14-91-10
eClass 8.1	27-14-91-10	eClass 9.0	27-14-44-33
eClass 9.1	27-14-44-33		

Product information

Descriptive text ordering data Other versions available on request. The blanking plugs must be tightened "hand-tight" with the screwdriver.

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN_WSCAD

Data sheet

**Blanking plugs
VP M20-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

