

**Blanking plugs  
VP M25-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Type	VP M25-MS65
Order No.	<a href="#">1777750000</a>
Version	Blanking plugs, Blanking plug, M 25, 7 mm, Brass, nickel-plated
GTIN (EAN)	4032248158027
Qty.	100 pc(s).

**Data sheet**

**Blanking plugs  
VP M25-MS65**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	11 mm	Length (inches)	0.433 inch
Height	11 mm	Height (inches)	0.433 inch
Net weight	14.26 g	Diameter	28 mm

**General information**

Cable gland	metric	External thread	M 25
Head diameter	28 mm	Length of thread	7 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Protection degree	IP68
Sealing	NBR		

**Classifications**

ETIM 3.0	EC000032	ETIM 4.0	EC000032
ETIM 5.0	EC000032	ETIM 6.0	EC000451
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-10
eClass 6.2	27-14-91-10	eClass 7.1	27-14-91-10
eClass 8.1	27-14-91-10	eClass 9.0	27-14-44-33
eClass 9.1	27-14-44-33		

**Product information**

Descriptive text ordering data      Other versions available on request. The blanking plugs must be tightened "hand-tight" with the screwdriver.

**Approvals**

Approvals



ROHS      Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN_WSCAD</a>

**Data sheet**

**Blanking plugs  
VP M25-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

