

TurboSwap MB171SP-B

Tray-Less 3.5" SATA HDD Mobile Rack



ICY DOCK®
www.icydock.com

**FULL METAL
CONSTRUCTION**



Fan Speed Control
Power Switch



2pin & 3pin
Fan Connector



5.25" BAY

All-Metal Arms

Ultra-Flex Shock Absorbing Kit

**80mm Fan
Standard**



**120mm Fan
Optional**



Full-Size 3.5" SATA HDD



Half-Height 3.5" SATA HDD



TurboSwap MB171SP-B Features & Specs

- * Tray less hot swappable drive cage
- * Fits full sized and half height 3.5" SATA drives up to 4TB into a single 5.25" bay
- * Supports up to 6Gb transfer speeds (depending on host configuration)
- * Heavy Duty all metal construction
- * Locking mechanism to protect your data
- * 80mm fan to keep your drives cool
- * Front panel fan speed control with power switch
- * Optional spacing available for aftermarket 120mm fans
- * 2 pin and 3 pin fan connections available
- * Shock absorbing anti vibration features

Model Number	MB171SP-B
Color	Black
Host Interface	7pin SATA connection
Drive Fit	3.5 " SATA 1.5 / 3 / 6 Gbit/s hard drive
Device Fit	5.25" half height device bay
Transfer Rate	Up to 6 Gb/sec. (depending on hard drive speed)
Power Input	15pin SATA power connection
Structure	Full Metal
Drive Cooling	80 x 80 x10mm cooling fan & metal heat dissipation
LED Indication	Power (solid blue) / HDD access (Flashing blue)
Package Contents	Device, user manual, 8 screws & 2 keys
Dimension (L x W x H)	145.8 x 41.25 x173mm
Weight	458.8g