

5 in 3 DataCage Classic

HDD BAY

ICY DOCK®
www.icydock.com

MB455SPF-B • 3.5" SATA Removable RAID
Backplane Module



SATA3
6Gb/s

3
YEARS
WARRANTY

DRIVE TRAY LEVER EJECTION BUTTON
DRIVE TRAY EXTRACTION LEVER

Anti Vibration Drive Tray

RESET BUTTON

FAN FAIL & OVERHEAT

HDD FAIL: RED LED

HDD ACCESS: AMBER LED

HDD POWER: GREEN LED

4 PIN MOLEX POWER
(REQUIRE TO CONNECT ALL POWER PORTS)

FAN CONNECTOR

BUZZER

SIGNAL OUT

HDD FAIL
SIGNAL IN

TEMP SET

HDD 1 HDD 2 HDD 3 HDD 4 HDD 5

MB455SPF-B 5 in 3 SATA Internal Raid Backplane

- * 5 in 3 RAID back plane module.
- * Support SATA 3 (6 Gb/s) hard drive.
- * Fits five 3.5" SATA hard drive *fully supports Hot-Swap function.*
- * Compact and space saving for multiple drives fit (*Five drives within three 5.25" bay fitting*).
- * Internal drive *security, exchangeability, expandability and maintenance capabilities.*
- * *Durable aluminum body* for excellent heat dissipation with stylish outlook.
- * *Detachable 80mm ball bearing rear cooling fan* for easy maintenance.
- * *Advanced drive monitoring system* built internally w/ visual and audio indicators.
- * *3 level temperature threshold settings* of 45° C, 55° C, and 65° C.
- * *Drive trays are interchangeable* with ICY DOCK FatCage (MB15X Series), DataCage Basic (MB876), DataCage Classic (MB45X Series), ICYBento (MB559 Series), ICYCube (MB561 Series).

Model Number	MB455SPF-B
Color	Black
Drive Fit	5 x 3.5" SATA 1.5 / 3 / 6 Gbit/s hard drives
Device Fit	3 x 5.25" half height device bay
Host Connection	5 x 7 pin SATA port
Power Input	3 x 4 pin Molex Power
Transfer Rate	Up to 6Gb/sec. (depending on hard drive speed)
Insert & Extract connection Via	Direct SATA hard drive connection
Structure	Aluminum body w/ partial plastic
Drive Cooling	Detachable rear outtake fan w/ aluminum heat dispersion
Alarm Indication	Auto & Visual
LED Indication	Drive power (green), activity (amber), failure (red) for each bay An individual (red) LED for fan failure and overheat
Dimension (L x W x H)	w/ fan 220.0 x 147.0 x 127.0 mm (w/o fan) 180.0 x 147.0 x 127.0 mm
Weight	3.60 lbs.