

# ToughArmor

## MB601VK-B

2.5" U.2 NVMe SSD Mobile Rack for 3.5" Bay

ICY DOCK®  
www.icydock.com



SUPPORT  
**nvm**  
EXPRESS®



Anti-Vibration Design



EZ-Slide Mini Tray System

3.5" Device Bay

Drive Tray Ejection Button

Cooling Airflow Vent



Security Key Lock

LED Indicator

● Green: Device Power

● Flashing: Drive Activity

NVMe Connection Port

**nvm**  
EXPRESS®  
Up to 32Gb/s

## MB601VK-B 2.5" SATA Mobile Rack Features

- \* Fits 1 x 2.5" U.2 NVMe SSD (NVMe U.2 host is required to access the drives)
- \* Fits any external 3.5" drive bay or floppy bay
- \* Supports NVMe 32Gb/s transfer rate
- \* Accommodates 2.5" SSD with 7mm-15mm Height
- \* Active Power Technology (APT) - only powers up if there is drive installed in the drive bay
- \* Anti-Vibration Technology (AVT) - creates a safe environment for hard drives or SSDs
- \* EMI Grounding - protects hard drives from electrical damage
- \* Eagle-hook lock system & 2-segment safeguard key lock keeps drives secure within the enclosure
- \* Heavy duty full metal construction, perfect for enterprise applications
- \* Drive tray is compatible with ToughArmor MB991SK-B, MB991IK-B, MB994SP-4S, MB994SP-4SB-1, MB994SK-1B, MB994IPO-3SB and MB991U3-1SB \*SAS / SATA SSD/ HDD only

Model Number	MB601VK-B
Host Interface	U.2 (SFF-8639)
Drive Fit	1 x NVMe U.2 SSD NVMe U.2 host is required to access drives
Device Bay	1 x External 3.5" Drive Bay
Transfer Rate	NVMe - Up to 32Gbps (depending on drive speed)
Power Input	via U.2 (SFF-8639)
Color	Matte Black
Structure	Full Metal
Drive Cooling	Metal heat dissipation
Drive Security	2-Segment key lock
LED Display Color	Green : Device Power ; Flashing : Drive Activity
Dimension (L x W x H)	161.2 x 101.2 x 25.4mm
Weight	397g