

ToughArmor

MB699VP-B



ICY DOCK®

www.icydock.com

4 x 2.5" U.2 NVMe SSD Mobile Rack for 5.25" Bay



nvm
EXPRESS

ToughArmor MB699VP-B
Next generation high speed data storage



Maximizing NVMe SSD

4 x miniSAS HD up to 32Gb/s
per channel



Full Metal Drive Tray



3 Speed
Fan Control
High / Low / Off

MB699VP-B U.2 NVMe Mobile Rack Features

- *Perfect for rugged applications and complies to flammability requirements
- *Fits 4 x 2.5" U.2 NVMe SSD
(NVMe U.2 host is required to accept NVMe SSD)
- *Supports NVMe 32Gb/s transfer rate
- *Fits any external 5.25" drive bay
- *Dual 40mm fans keep your drives from overheating
- *Requires only 2 x 15pin power connectors to power all 4 bays
- *Anti-Vibration Technology (AVT) - creates a safe environment for hard drives or SSDs
- *Active Power Technology (APT) - individual led & cooling fan only powers up if there is a drive installed in the bay
- *Eagle-hook lock system keeps drives secured within the enclosure
- *Removable tray system for easy maintenance and hot-swap
- *Industry leading 3 year warranty w/ exceptional customer support

Model Number	MB699VP-B
Host Interface	U.2 (SFF-8643)
Drive Fit	4 x NVMe U.2 SSD
	NVMe U.2 host is required to access drives
Compatible Drive Height	Up to 15mm drive height
Device Bay	1 x External 5.25" Drive Bay
Transfer Rate	NVMe - Up to 32Gbps (depending on drive speed)
Power Input	2 x 15pin SATA power
Structure	Full Metal
Drive Cooling	Dual 40mm rear cooling fan
Hot-Swap	Yes
LED Display Color	Green : Device Power / Flashing : Drive Activity
Dimension (L x W x H)	170 x 146 x 41.3mm
Weight	865g