

tesa® 4662 Strong duct tape

tesa® 4662 is a strong duct tape. It consists of a 27 mesh woven PET/cotton fabric backing coated with a natural rubber adhesive.

tesa® duct 4662 is a self adhesive tape with typical duct features for a wide range of applications.

Features:

- excellent adhesion even on rough and dusty surfaces (e.g. brickwork, timber)
- water repellent
- conformable
- available in 3 colours: black, white, silver

Main Application

- Sealing of pipes and ducts
- Bonding of construction and protection films
- Closing of covering foils
- Application on brickwork and timber
- Fixing, closing, packaging and a lot more!

Technical Data

▪ Backing material	PE laminated cloth	▪ Elongation at break	18 %
▪ Total thickness	230 µm	▪ Tensile strength	30 N/cm
▪ Type of adhesive	natural rubber	▪ Temperature resistance (30 min)	95 °C
▪ Adhesion to steel	4.4 N/cm	▪ Mesh	27 count per square inch

Properties

▪ Hand tearability	●●●	▪ Abrasion resistance	●●
▪ Straight tear edges	●●●	▪ Water resistance	●●

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=04662>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.