



# <sup>3</sup>/<sub>8</sub>" Concealed-Mount Contacts, Wide Gap, Stubby

## SM-207-5LO/BR

1" (25mm) Gap, Closed Loop, with Stubby 3/4" (19mm) Switch, Brown SM-207-5LO/W

1" (25mm) Gap, Closed Loop, with Stubby 3/4" (19mm) Switch, White



- Used for protecting sliding doors and windows where space is limited
- 3/8" Press-fit mount
- 15" (38cm) wire leads
- Contact reed switch is SPST, deactivated rhodium on gold under-plating for a longer expected life
- Unique glue/epoxy compound protects reed switch
- For closed loop circuits
- 1" (25mm) Gap
- Lifetime limited warranty





SM-207-5LQ/BR Shown




15" Wire-Leads



# Specifications:

| Model number      |         | SM-207-5LQ/BR  | SM-207-5LQ/W |
|-------------------|---------|--|--------------|
| Circuit type      |         | Closed loop  |              |
| Operation gap     |         | 1" (25mm)  |              |
| Color             |         | Brown  | White        |
| Leads             |         | Pre-wired 15", #22   |              |
| Material          | Case    | High-impact ABS plastic / epoxy compound   |              |
|                   | Contact | Deactivated rhodium on gold under-plating  |              |
| Contact rating    |         | 0.1A@100VDC (max)  |              |
|                   |         | 1.0A@10VDC (max)   |              |
|                   |         | 10W (max)  |              |
| Temperature       |         | -15°~160°F (-25°~70°C)   |              |
| Switch cycles     |         | 50 Million (0.1mA@5VDC)  |              |
| Switch dimensions |         | <sup>3</sup> / <sub>4</sub> "x <sup>7</sup> / <sub>16</sub> "x <sup>3</sup> / <sub>8</sub> " (19x11x9mm)   |              |
| Magnet dimensions |         | 1 <sup>3</sup> / <sub>8</sub> "x <sup>7</sup> / <sub>16</sub> "x <sup>3</sup> / <sub>8</sub> " (35x11x9mm) |              |
| Magnet            |         | Alnico 5   |              |

#### **Dimensions:**



### SECO-LARM® U.S.A., Inc.

16842 Millikan Avenue, Irvine, CA 92606

Phone: (949) 261-2999 | (800) 662-0800 Fax: (949) 261-7326

Website: www.seco-larm.com Email: sales@seco-larm.com

Copyright 2015 © SECO-LARM U.S.A., Inc. All rights reserved.

All trademarks are the property of SECO-LARM U.S.A., Inc. or their respective owners.

The SECO-LARM policy is one of continual development. For that reason, SECO-LARM reserves the right to change prices and specifications without notice. SECO-LARM is not responsible for misprints.

