

# COMP-CARD®-System

## SMC-12

### Aluminium Electrolytic Capacitors, SMD 16 Values / 325 Pieces



<b>Nova Article No.</b>	SMC-12
<b>Brand of Components</b>	TEAPO
<b>Type</b>	<a href="#">EV</a>
<b>Tolerance</b>	±20%
<b>Temperature</b>	-55 bis +105°C
<b>Life time</b>	2.000 hrs
<b>Number of Values</b>	16
<b>Quantity per Value</b>	see Value-Quantity-Selection
<b>Total Quantity</b>	325
<b>Ring Binder</b>	No
<b>Flap</b>	1 x FL16/20
<b>Note</b>	D4/D5/D6/D8/D10 = Diameter

#### Value-Quantity-Selection 6V

20 x 22µF (D4)      20 x 47µF (D4)      15 x 100µF (D5)      10 x 220µF (D8)

#### Value-Quantity-Selection 16V

20 x 10µF (D4)      20 x 22µF (D4)      15 x 47µF (D5)      15 x 100µF (D6)  
10 x 220µF (D8)

#### Value-Quantity-Selection 35V

20 x 4,7µF (D4)      20 x 10µF (D4)      15 x 22µF (D5)      10 x 100µF (D8)  
80 x 220µF (D10)

#### Value-Quantity-Selection 50V

20 x 1,0µF (D4)      15 x 10µF (D5)



Nova Elektronik GmbH, Sachsstr. 6, 50259 Pulheim

[www.nova-elektronik.de](http://www.nova-elektronik.de)

For any questions, please contact : [Info@nova-elektronik.de](mailto:Info@nova-elektronik.de)