

Wiha Cabinet Tip Slotted & Phillips Screwdrivers



186 Slotted Cabinet Tip Screwdriver, With Wiha-Square Handle Blade CVM steel, hardened, nickel-plated. Tip parallel to shaft. Series includes extra long dimensions for screws in difficult to reach locations. Wiha-square handle cellulose-acetate, impact resistant.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
18601	2.0	.08	40	1.6	0.40	.02	100	4.0	14	.55	.02	10
18603	2.5	.10	50	2.0	0.40	.02	110	4.3	14	.55	.02	10
18606	3.0	.12	75	3.0	0.50	.02	150	5.9	19	.75	.05	10
18609	3.0	.12	100	3.9	0.50	.02	175	6.9	19	.75	.06	10
18612	3.0	.12	150	5.9	0.50	.02	225	8.9	19	.75	.06	10
18615	3.0	.12	200	8.0	0.50	.02	285	11.2	22	.87	.08	10
18624	4.0	.16	100	3.9	0.60	.02	185	7.3	22	.87	.08	10
18627	4.0	.16	150	5.9	0.60	.02	235	9.3	22	.87	.10	10
18630	4.0	.16	200	8.0	0.60	.02	285	11.2	22	.87	.11	10
18645	5.0	.20	150	5.9	0.70	.03	245	9.6	24	.94	.15	10
18648	5.0	.20	200	8.0	0.70	.03	295	11.6	24	.94	.17	10
18651	5.0	.20	300	12.0	0.70	.03	395	15.6	24	.94	.20	10
18654	6.0	.24	100	3.9	0.90	.04	205	8.1	28	1.10	.19	10
18657	6.0	.24	150	5.9	0.90	.04	255	10.0	28	1.10	.21	10
18663	6.0	.24	300	12.0	0.90	.04	405	15.9	28	1.10	.29	10
18678	8.0	.32	300	12.0	1.20	.05	415	16.3	32	1.26	.39	10
18681	10.0	.39	200	8.0	1.60	.06	315	12.4	32	1.26	.37	10



153 Phillips Screwdriver, With Wiha-Square Handle Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Wiha-square handle cellulose-acetate, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
15305	0	60	2.4	3.0	.12	135	5.3	19	.75	.05	10
15310	1	80	3.1	4.5	.18	175	6.9	24	.94	.11	10
15315	1	200	8.0	4.5	.18	295	11.6	24	.94	.15	10
15325	2	100	3.9	6.0	.24	205	8.1	28	1.10	.18	10
15330	2	250	10.0	6.0	.24	355	14.0	28	1.10	.27	10
15335	2	350	13.7	6.0	.24	455	17.8	28	1.10	.33	10
15340	3	150	5.9	8.0	.32	265	10.4	32	1.26	.33	10



222 Pozidriv® Screwdriver, With Wiha-Square Handle Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Wiha-square handle cellulose-acetate, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
22220	1	200	8.0	4.5	.17	295	11.6	.15	10
22230	2	250	9.8	6.0	.23	355	13.9	.27	10
22240	3	150	5.9	8.0	.31	265	10.4	.30	10

Wiha Offset Screwdrivers



161 Phillips Offset Screwdriver, With

Handle For working in confined spaces. Blade CVM special steel, hardened, hard chromed. Handle high quality plastic, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	lbs.	Pkg.
16112	1 + 2	125	4.9	5.5	.217	.08	10
16134	3 + 4	200	8.0	10.0	.315	.33	10



207 Slotted Offset Screwdriver, With Handle

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	Pkg.
20700	3.5	9/64	90	3.5	0.6	.02	.02	10
20705	4.0	5/32	100	3.9	0.8	.03	.03	10
20710	5.5	7/32	125	5.0	1.0	.04	.06	10
20715	6.5	1/4	125	5.0	1.2	.05	.07	10
20720	8.0	5/16	150	5.9	1.2	.05	.15	10
20725	10.0	3/8	175	6.9	1.6	.06	.23	10



20790 5 Piece Slotted & Phillips Offset Screwdriver Set

Item No.	lbs.	Set includes:
20790	.92	Slotted: 6.5, 8.0, 10.0 Phillips: 1 + 2, 3 + 4



207 TORX® Offset Screwdriver With

Molded Handle Working in confined spaces. CVM special steel, hardened, black finish.

Item No.	Size	lbs.	pkg.
20756	T6 + T8	.02	1
20757	T7 + T9	.02	1
20758	T10 + T15	.02	1
20759	T20 + T25	.07	1
20760	T27 + T30	.10	1



20799 TORX® Offset Screwdriver Set, 5 Pcs. Molded Handle.

Item No.	T6+T8, T7+T9, T10+T15, T20+T25, T27+T30	lbs.	pkg.
20799		.24	1