



Wiha Pico Soft Grip TORX®



267 TORX® Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	Size	mm	Inch	mm	Inch	Pkg.
26732	T1	40	1.6	134	5.3	10	
26733	T2	40	1.6	134	5.3	10	
26735	T3	40	1.6	134	5.3	10	
26736	T4	40	1.6	134	5.3	10	
26737	T5	40	1.6	134	5.3	10	
26739	T6	40	1.6	140	5.5	10	
26741	T7	40	1.6	140	5.5	10	
26743	T8	40	1.6	140	5.5	10	
26745	T9	50	2.0	150	5.9	10	
26747	T10	50	2.0	150	5.9	10	
26749	T15	60	2.4	160	6.3	10	
26751	T20	60	2.4	160	6.3	10	

*Metric dimensions actual - Inch dimensions approximate

In storage pouch



26793 8 Pc. TORX® Precision Driver Set, With Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit.

Item	TORX®:	lbs.
No.	T1, T2, T3, T4, T5, T6, T7, T8	.50

In storage pouch



26796 8 Pc. TORX® Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit.

Item	TORX®:	lbs.
No.	T5, T6, T7, T8 x 40mm	.57
26796	T9, T10 x 50mm, T15, T20 x 60mm	

Pico Soft Grip Hex Inch & Metric



263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	Inch	mm	Inch	mm	Inch	Pkg.
26341	.028(0.7)	40	1.6	134	5.3	10	
26343	.035(0.9)	40	1.6	134	5.3	10	
26345	.050(1.3)	40	1.6	134	5.3	10	
26349	5/64(2.0)	50	2.0	150	5.9	10	
26363	1/16	50	2.0	144	5.7	10	
26367	3/32	60	2.4	160	6.3	10	
26369	7/64	60	2.4	160	6.3	10	
26371	1/8	60	2.4	160	6.3	10	

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

26392 8 Piece Hex Inch Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed.

Item	Hex Inch:	lbs.
No.	.028, .035, .050 x 1.6"	.24
26392	5/64, 1/16 x 2.0", 3/32, 7/64, 1/8 x 2.4"	



263 Hex Metric Driver, With Precision Soft PicoFinish Handle

Item	No.	mm	mm	Inch	mm	Inch	Pkg.
26341	.7(.028)	40	1.6	134	5.3	10	
26343	.9(.035)	40	1.6	134	5.3	10	
26345	1.3(.050)	40	1.6	134	5.3	10	
26347	1.5	50	2.0	144	5.7	10	
26349	2.0(5/64)	50	2.0	150	5.9	10	
26351	2.5	60	2.4	160	6.3	10	
26353	3.0	60	2.4	160	6.3	10	

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

26393 7 Piece Hex Metric Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Metric:	lbs.
26393	.71, .89, 1.27 x 40mm	.22
	1.5, 2.0 x 50mm, 2.5, 3.0 x 60mm	

Pico Soft Grip Ball End Inch & Metric



264 Ball End Hex Inch Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	Inch	Inch	mm	Inch	mm	pkg.
26455	1/16	2.0	50	5.9	150	10	
26457	5/64	2.0	50	5.9	150	10	
26459	3/32	2.0	50	5.9	150	10	
26461	7/64	2.4	60	6.3	160	10	
26463	1/8	2.4	60	6.3	160	10	
26465	9/64	2.4	60	6.3	160	10	
26467	5/32	2.4	60	6.3	160	10	

*Metric dimensions actual - Inch dimensions approximate



26493 7 Pc. Inch Ball End Hex Precision Driver Set, With Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item	Ball End Hex Inch:	lbs.
No.	1/16, 5/64, 3/32 x 2.0"	.27
26493	7/64, 1/8, 9/64, 5/32 x 2.4"	



264 Ball End Hex Metric Screwdriver, With Precision Soft PicoFinish Handle. Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	mm	mm	Inch	mm	Inch	pkg.
26441	1.3	40	1.6	134	5.3	10	
26443	1.5	50	2.0	150	5.9	10	
26445	2.0	50	2.0	150	5.9	10	
26447	2.5	60	2.4	160	6.3	10	
26449	3.0	60	2.4	160	6.3	10	

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Precision Chip Lifter



26815 Soft PicoFinish Precision Chip Lifter Blade CVM steel, hardened, hard chromed.

Item	mm	mm	mm	mm	Inch
No.	1	3.5	50	150	5.9
26815	Standard Soft PicoFinish handle				